

TECHSPEC® 15mm Dia. x 60mm FL, NIR II, Inked, Double-Convex Lens



Stock #67-636-INK

CONTACT US

Other Coating Options

-

1

+

£44.63

ADD TO CART

Qty 1-9
£44.63
Qty 10+
£40.16
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):

15.00 ±0.025

Back Focal Length BFL (mm):

59.00
Effective Focal Length EFL (mm): 60.00
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.08
Radius R₁=R₂ (mm): 61.5
Clear Aperture CA (mm): 14.00
f/#: 4.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1.00
Numerical Aperture NA: 0.13
Type: Double-Convex Lens
Wavelength Range (nm): 750 - 1550
Damage Threshold, By Design: ☐ 8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View