See all 88 Products in Family

15mm Dia. x 8.25mm FL, NIR I Coated, Molded Aspheric Condenser Lens

Molded Aspheric Condenser Lenses

Stock **#15-887** CONTACT US

Other Coating Options

- 1 + **£50**.00

ADD TO CART

Volume Pricing	
Qty 1-10	**£50.00** each
Qty 11-49	**£44.00** each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Condenser Lens

Note:

Click here for more information on the ISO 10110 surface quality specification.

Physical & Mechanical Properties

Diameter (mm):
15.00 +/-0.3

Centering (arcmin):
≤25

Clear Aperture CA (mm):
12.00

Edge Thickness ET (mm):
2.0

Center Thickness CT (mm):
8.50 (nominal)

Bevel:
Protective as needed

Diameter of Asphere (mm):
15.0

Shape of Back Surface:
Convex

Optical Properties

Effective Focal Length EFL (mm):
8.25 @ 587.6nm

Numerical Aperture NA:
0.91

Back Focal Length BFL (mm):
7.96

Substrate:
Liba2000+

Focal Length Tolerance (%):
±7

Coating:
NIR I (600-1050nm)

Coating Specification:
R_{avg} ≤0.5% @ 600 - 1050nm

Surface Quality:
5/3 x 0.4; E 0.2

f/#:
0.55

Abbe Number (v_d):
58.85

Index of Refraction (n_d):
1.520

Radius R_2 (mm):
27.3

Wavelength Range (nm):
600 - 1050

Conjugate Distance:
Infinite

Focal Length Specification Wavelength (nm):
587.6

Material Properties

Coefficient of Thermal Expansion CTE (10^{-6}/°C):
9.4

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 242:
Compliant

Product Details

- Hardened for Improved Durability
- High Numerical Apertures
- Ideal for Illumination Applications

Molded Aspheric Condenser Lenses are pressed, hardened, and annealed to meet precise optical and mechanical specifications. The hardening process improves the durability of the lenses, making them less susceptible to thermal shock and scratching than traditionally polished lenses. These Molded Aspheric Condenser Lenses are ground and polished on the second surface, enhancing the overall precision of the lenses. Molded Aspheric Condenser lenses are ideal for a wide range of illumination and detection applications, including biotech instruments such as DNA sequencers and polymerase chain reaction (PCR) testing platforms.

Technical Information



Compatible Mounts

;