


15mm Diameter Laser Diode Mirror



Stock #43-854 **20+ In Stock**

⊖ 1 ⊕ £23⁰⁰

ADD TO CART

Volume Pricing

Qty 1-10	£23.80 each
Qty 11-24	£18.40 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Flat Mirror

Type:

Physical & Mechanical Properties

15.00 ±0.25

Diameter (mm):

3.00

Thickness (mm):

Dimensional Tolerance (mm):

±0.25

Optical Properties

Coating Type:

Dielectric

Coating:

Dielectric Mirror (500-700nm)

Design Wavelength DWL (nm):

633

Substrate:

Float Glass

Coating Specification:

R_{abs} >97% @633nm

Surface Quality:

80-50

Environmental & Durability Factors

Durability:

ML-C-48497A

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Compliant](#)


Product Details

- Over 95% Reflectance of Visible Laser Diode Light
- Ideal for Multiple Reflection Systems
- Coating Optimized for 633nm at 45° AOI

Visible Laser Diode Mirrors are specially coated to attain maximum reflection of visible laser diodes. Optimized for 633nm at a 45° angle of incidence, these mirrors provide 97% reflectance versus only 85 - 90% for standard first surface mirrors. This reduced loss is particularly important in multiple reflection systems, where loss can significantly impact system efficiency. Visible Laser Diode Mirrors feature a float glass substrate and are ideal for multiple reflection systems.

Technical Information

Visible Laser Diode Mirror Reflectance at 45°



@ 500nm	95.0%
@ 550nm	97.0%
@ 600nm	97.5%
@ 633nm	97.0%
@ 635nm	97.0%
@ 650nm	96.5%
@ 670nm	96.0%
@ 675nm	95.0%
@ 700nm	94.5%

Quote Your Size

Compatible Mounts

