

TECHSPEC[®] 15mm Max Aperture Motorizable Iris



High Performance Motorizable Iris



Stock #34-289 3 In Stock

-

1

+

£70⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	£70.00 each
Qty 5-9	£61.92 each
Qty 10-25	£57.28 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Unmounted

Type:

Physical & Mechanical Properties

15.0	Maximum Aperture (mm):
24.0	Outer Diameter (mm):
Brass-Spring Steel	Construction:
12	Number of Leaves:
5.00	Thickness (mm):
21.3	Pitch Diameter (mm):

Optical Properties

1.2	Minimum Aperture (mm):
-----	------------------------

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

Product Details

- Fast Accurate Repeatable Motion
- Dual Control Gear and Lever Mechanics
- Removable Pin for OEM Integration
- Anti-Reflection (AR) Leaves Available
- Iris Diaphragm Mounts and Motor Sold Separately

TECHSPEC® High Performance Motorizable Irises are designed for integration into custom applications and for use in a lab environment. These irises include two methods for controlling the aperture size: one by a standard pin which enables standard angular deviation and the other that duplicates the movement of the pin by replicating the teeth of a spur gear on the inner housing of the iris. This feature allows for custom motion control in conjunction with a compatible spur gear. TECHSPEC® High Performance Motorizable Irises maintain fast, accurate, and repeatable movement to any location through the iris's range of motion. The 7mm, 12mm, 22mm, 28mm, and 34mm Max Aperture configurations are also available with Anti-Reflection (AR) Leaves.

Technical Information

