

160mm x 100mm x 12mm Metric Lab Jack



Stock **#54-687** 8 In Stock

-

1

+

£796^{.71}

ADD TO CART

Volume Pricing	
Qty 1+	£796.71 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Universal (Metric & English)

Type:

Physical & Mechanical Properties

Linear (Z)

Type of Movement:

Pantograph	Guide System:
160 x 100	Stage Size (mm):
Aluminum, Brass, & Stainless	Construction:
42	Height Adjustment (mm):
1	Leadscrew Pitch (mm):
25	Load Capacity (kg):
123	Maximum Height (mm):
81	Minimum Height (mm):
3.2	Weight (kg):
0.1 (typical)	Parallelism (mm):

Hardware & Interface Connectivity

Lead Screw	Type of Drive:
------------	----------------

Threading & Mounting

Mounting Threads:
Top: (17) ¼-20, (8) M4 x 0.7 Bottom: (4) M6 x 1 on 140 x 80mm, (4) 7.5mm thru on 76.2 x 80mm, (4) 4.5mm thru on 50mm Sq.

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

PRODUCT DETAILS

- Rugged, Black Anodized Aluminum Construction
 - Fine Lead Screw for Precision Movement
 - Large Adjustment Knob for Maximum Control
 - Locking Knob to Secure Vertical Positioning
- Metric Labs Jacks feature a rugged construction and a fine screw movement that allows for precision adjustment of vertical positioning of most optical components or equipment, with a maximum weight capacity of up to 55 lbs. Top surfaces are precision finished mounting platforms with ¼-20 and M4 tapped holes (see diagram). The bottom platforms have several additional M6 metric and ¼-20 English sized clearance holes, which are spaced to adapt to common mounting surfaces. Metric Lab Jacks utilize a locking knob to fix vertical position at desired height. Each full revolution of the adjustment knob moves the platform vertically by 1mm.
- These metric lab jacks offer stable, height-adjustable platforms ideal for laboratory and optical systems requiring manual vertical positioning. Designed for durability and repeatability, each lab jack integrates smoothly with breadboards, post assemblies, and manual translation stages. Their compact footprint and metric compatibility make them well-suited for modular lab setups where vertical lift precision and load stability are essential.
- 160 x 100mm Lab Jack ([#54-687](#)) and 132 x 80mm Lab Jack ([#56-336](#)) are compatible with the following stages: [#55-032](#), [#55-459](#), [#55-527](#), [#55-840](#), and [#55-841](#).
- Note:** Mount Lab Jacks on Metric or English Breadboards using [#12-796](#) to mount [#56-336](#) and [#54-687](#), and use [#12-797](#) to mount [#62-009](#).

TECHNICAL INFORMATION

#54-687

