

TECHSPEC® 16mm f/1.8, HPi Series Fixed Focal Length Lens



16mm HPi Series Fixed Focal Length Lens

Stock #33-814 **20+ In Stock**

⊖ 1 ⊕ £568.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£568.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

HPi Series **Product Family:**
Fixed Focal Length Lens **Type:**

Imaging Lens Type:
High Performance Lens with Fixed Apertures and Compact Form Factor

Physical & Mechanical Properties

Fixed	Iris Option:
64.20	Length (mm):
48	Maximum Diameter (mm):
48	Outer Diameter (mm):
117	Weight (g):
0	Maximum Rear Protrusion (mm):

Optical Properties

127mm - 53°	Horizontal Field of View @ Max Sensor Format:
Horizontal: 112.4mm - 47.2° Vertical: 82.7mm - 35.9° Diagonal: 144.7mm - 58°	Field of View at Max Sensor Format:
113.4mm - 47.6°	Horizontal Field of View, 1.1" Sensor:
101.3mm - 43.2°	Horizontal Field of View, 1" Sensor:
68.4mm - 30.1°	Horizontal Field of View, 2/3" Sensor:
55.7mm - 24.8°	Horizontal Field of View, 1/1.8" Sensor:
49.4mm - 22.1°	Horizontal Field of View, 1/2" Sensor:
44.7mm - 20.0°	Horizontal Field of View, 1/2.5" Sensor:
36.9mm - 16.6°	Horizontal Field of View, 1/3" Sensor:
27.6mm - 12.5°	Horizontal Field of View, 1/4" Sensor:
17.60	Maximum Image Circle (mm):
0.0353	Numerical Aperture NA, Object Side:
9 (7)	Number of Elements (Groups):
16.00	Focal Length FL (mm):
100 - ∞	Working Distance (mm):
f/1.8	Aperture (f/#):
N4 MgF ₂	Coating:
N4 MgF ₂	Coating Specification:
27.28	Entrance Pupil Position (mm):
40.34	Object Space Principal Plane (mm):
4.08	Image Space Principal Plane (mm):
-3.76	Maximum Distortion (%):
-58.81	Exit Pupil Position (mm):
400 - 2000	Optimized Working Distance (mm):
VIS	Lens Wavelength Range:

Sensor

1"	Optimized Sensor Format:
1.1"	Maximum Sensor Format:
1.85	Pixel Size (μm):

Threading & Mounting

Filter Thread:
M46.0 x 0.75 (Female)

Mount:
C-Mount

Environmental & Durability Factors

Storage Temperature (°C):
-20 to +60

Type of Ruggedization:
Industrial (Fixed Aperture with Simplified Mechanics)

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details


- 1.1", C-Mount Lens
- Up to 20 MegaPixels, 1.85µm Pixel Size Sensors
- Instrumentation (HPI) versions of our HP Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 16mm to 50mm Focal Length
- [Ruggedized \(HPr\) Designs](#) Also Available

TECHSPEC® HPI Series Fixed Focal Length Lenses offer the same high resolution performance as the TECHSPEC HP Series Lenses with a streamlined design. The simplified mechanical design enables a more compact size with a reduction in cost and weight, making them ideal for OEM volume applications. Featuring a wide range of fixed aperture versions and an adjustable focus, TECHSPEC HPI Series Fixed Focal Length Lenses offer the ideal combination of simplicity and flexibility required for industrial applications. Call for OEM Quantity Pricing.


Edmund Optics has created a family of high performance optical designs (the HP Series family) and developed three customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the HP Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- **HP Series:** Features locking cam focus and iris adjustment. This is the most adjustable version of these optical designs and is the typical high quality machine vision lens.
- **HPI Series:** Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.
- **HPr Series:** All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.


Technical Information




#33-814, 16mm f/1.8, HPI Series Fixed Focal Length Lens, Distortion Plot




#33-814, 16mm f/1.8, HPI Series Fixed Focal Length Lens, Relative Illumination Plot




#33-814, 16mm f/1.8, HPI Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#33-814, 16mm f/1.8, HPI Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 500mm Working Distance, f1.8



#33-814, 16mm f/1.8, HPI Series Fixed Focal Length Lens, Depth of Field Plot, 500mm Working Distance, f1.8



#33-814, 16mm f/1.8, HPI Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 1000mm Working Distance, f1.8



#33-814, 16mm f/1.8, HPI Series Fixed Focal Length Lens, Depth of Field Plot, 1000mm Working Distance, f1.8

Compatible Cameras