

**TECHSPEC® 15mm, Uncoated, High Tolerance N-BK7 Right Angle Prism**



N-BK7 High Tolerance Right Angle Prisms

Stock #32-545 **20+ In Stock**

⊖ 1 ⊕ £77<sup>20</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	£77.20 each
Qty 6-25	£61.60 each
Qty 26-49	£58.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Right Angle Prism **Type:**

**Physical & Mechanical Properties**

+0/-0.1 **Dimensional Tolerance (mm):**

**Bevel:**

Protective as needed

Length of Hypotenuse (mm):

21.20

Length of Legs (mm):

15.00

## Optical Properties

Angle Tolerance (arcsec):

±15

Coating:

Uncoated

Substrate:

N-BK7

Surface Quality:

40-20

Image Orientation:

Left-Handed

Ray Deviation (°):

90

Wavelength Range (nm):

350 - 2200

Power (fringes) @ 632.8nm:

1.25

Irregularity (fringes) @ 632.8nm:

0.25

## Regulatory Compliance

RoHS 2015:

Compliant

Reach 219:

Compliant

Certificate of Conformance:



[View](#)

## Product Details

- Ray Deviation of 90°
- Left Handed Image
- Low Arcsecond Angle Tolerance
- Additional [Right Angle Prism](#) Options Available

TECHSPEC® High Tolerance N-BK7 Right Angle Prisms are generally used to bend image paths or redirect light at 90°. This process produces a left-handed image, depending on the prism's orientation, the image may be inverted or reverted. Right angle prisms can also be combined for image/beam displacement. TECHSPEC® High Tolerance N-BK7 Right Angle Prisms feature low arcsecond angle tolerance and are made from precision N-BK7 for use in a variety of visible light applications. These prisms are available uncoated, with a protective aluminum overcoat, or MS<sup>®</sup> & aluminized.

## Technical Information





*Right Angle Prism Ray Path*



*Right Angle Prism Ray Path*



*Right Angle Prism Tunnel Diagram*



*Right Angle Prism Tunnel Diagram*