

[See all 22 Products in Family](#)

1.7mm FL, CS-Mount, Auto Iris, Wide Angle Lens



Image represents #22-793; Design will vary by stock number.

Stock **#22-794** **6 In Stock**

⊖ 1 ⊕ £258⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£258.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Product Family:
Low Distortion Wide Angle Lenses

Type:
Fixed Focal Length Lens

Physical & Mechanical Properties

Iris Option:
DC Auto Iris

Length (mm):

56.00

49 **Maximum Diameter (mm):**

49 **Outer Diameter (mm):**

51 **Weight (g):**

Optical Properties

Horizontal Field of View @ Max Sensor Format:
120°

Horizontal Field of View, 1/3" Sensor:
94°

Maximum Image Circle (mm):
7.20

Focal Length FL (mm):
1.70

Working Distance (mm):
300 - ∞

Aperture (f/#):
F/1.8 - Closed

Distortion (%):
<1

Maximum Distortion (%):
<1

Lens Wavelength Range:
VIS

Sensor

Maximum Sensor Format:
1/2.5"

Pixel Size (µm):
4.50

Threading & Mounting

Filter Thread:
N/A

Mount:
CS-Mount

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- Up to 1/2.5", C-Mount and CS-Mount options
- Up to 3 MegaPixel and Down to 1% Distortion
- No Refocusing from 100mm to Infinity
- 1.28mm to 40mm Focal Length

Low Distortion Wide Angle Lenses maintain high resolution for applications with long working distance requirements and can accommodate multi-megapixel camera sensors. The optical design of these low-distortion wide-angle lenses enables users to achieve less than 3% distortion over a 125° field of view, or less than 1% distortion over a 110° field of view. These lenses feature a locking screw for the manual iris enabling the use in high vibration environments. Low Distortion Wide Angle Lenses are ideal for security and surveillance, machine vision, or [factory automation](#) applications. These lenses do not require refocusing from 100mm to Infinity.

Note: Image will be flipped (180° rotation). Auto Iris Options require cameras with P-Iris or DC Iris control.