

Richardson Gratings™ 1800 Grooves, 25 x 25mm, 190-900nm, Plane Holographic
Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Reflective Holographic Diffraction Gratings



Stock **#15-749** **4 In Stock**

-

1

+

£144⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	£144.00 each
Qty 10-24	£129.60 each
Need More?	Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Reflective Diffraction Grating

Master Reference:

300H	
Physical & Mechanical Properties	
25.0 x 25.0 ±0.1	Dimensions (mm):
>90	Clear Aperture (%):
Holographic Grating	Construction:
25.00	Length (mm):
6.00 ±0.5	Thickness (mm):
25.00	Width (mm):
±1	Centering of Ruled Area on Substrate (mm):
±0.15	Alignment of Grooves to Edge (°):
<0.05	Groove Spacing Tolerance (%):
Optical Properties	
1800	Groove Density (grooves/mm):
190 - 900	Wavelength Range (nm):
250	Blaze Wavelength (nm):
Aluminium	Coating:
Float Glass	Substrate: □
λ/4	Reflected Wavefront, RMS:
S, P and Average	Polarization:
1	Spectral Order (m):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- High Diffraction Efficiency
 - Reduced Stray Light and More Accurate Periodicity than Ruled Gratings
 - Wavelength Options from UV to NIR Regions Available
 - Custom Sizes Available
- Richardson Gratings™ High Precision Reflective Holographic Diffraction Gratings display reduced light scattering compared with ruled gratings, making them ideal for stray light sensitive applications such as Raman spectroscopy. The gratings are recorded in a photoresist by exposure to an intense laser interference pattern and then chemically developed to reveal a fringe pattern with a sinusoidal cross section. Gratings for use from the UV to NIR spectral regions are available.
- Note:** The surface of these gratings is very sensitive and should never be touched when handling the optic. If cleaning is required to remove dust particles, non-contact cleaning using clean compressed air is recommended.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
 - High-precision surface quality and flatness
 - Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
-