


1.65μm, 50mm Diameter, Infrared Longpass Filter



Infrared (IR) Longpass Filters

Stock **#68-658** 3-4 DAYS



1



£396.95

ADD TO CART

Qty 1-9

£396.95

Qty 10+

£356.66

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
50.00 +0.0/-0.1

Optical Density OD (Average):
≥3.0

Cut-On Wavelength (nm):
1,650.00

Substrate: Silicon (Si)
Operating Temperature (°C): -62 to +71
Coating: Traditional Coated
Surface Quality: 80-50
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.2
Transmission (%): >85
Transmission Wavelength (nm): 1730 - 3300
Transmission Wavelength (µm): 1.73 - 3.30
Type: Longpass Filter
Blocking Wavelength Range (nm): 200 - 1650
Parallelism (arcmin): <10
Clear Aperture (%): 90
Slope Factor (%): <7
Cut-On Wavelength (µm): 1.65 ±0.07
Note: Transmission at cut-on wavelength is 5% of peak transmission.
Surface Flatness (P-V): 3 - 5λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant