

1.67mm FL C-Mount, Manual Iris, Wide Angle Lens



1.67mm FL C-Mount, Manual Iris, Wide Angle Lens, #68-695

Stock **#68-695** **5 In Stock**

-

1

+

£522⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£522.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Low Distortion Wide Angle Lenses	Series:
Fixed Focal Length Lens	Type:

Physical & Mechanical Properties

Variable	Iris Option:
	Length (mm):

56.00	
36.0	Maximum Diameter (mm):
36	Outer Diameter (mm):
80.00	Weight (g):

Optical Properties	
110°	Horizontal Field of View, 1/3" Sensor:
7.20	Maximum Image Circle (mm):
1.67	Focal Length FL (mm):
100 - ∞	Working Distance (mm):
f/1.8 - Closed	Aperture (f/#):
<1	Distortion (%):
<1	Maximum Distortion (%):
VIS	Lens Wavelength Range:

Sensor	
1/2.5"	Maximum Sensor Format:
4.50	Pixel Size (µm):

Threading & Mounting	
N/A	Filter Thread:
C-Mount	Mount:

Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 223:
View	Certificate of Conformance:

Product Details

- Up to 1/2.5", C-Mbunt and CS-Mount options
 - Up to 3 MegaPixel and Down to 1% Distortion
 - No Refocusing from 100mm to Infinity
 - 1.28mm to 40mm Focal Length
- Low Distortion Wide Angle Lenses maintain high resolution for applications with long working distance requirements and can accommodate multi-megapixel camera sensors. The optical design of these low-distortion wide-angle lenses enables users to achieve less than 3% distortion over a 125° field of view, or less than 1% distortion over a 110° field of view. These lenses feature a locking screw for the manual iris enabling the use in high vibration environments. Low Distortion Wide Angle Lenses are ideal for security and surveillance, machine vision, or [factory automation](#) applications. These lenses do not require refocusing from 100mm to Infinity.
- Note:** Image will be flipped (180° rotation). Auto Iris Options require cameras with P-Iris or DC Iris control.