

TECHSPEC® 16mm, f/11 UCi Series Fixed Focal Length Lens



16mm UCi Series Fixed Focal Length Lens



Stock #33-888 **20+ In Stock**

⊖ 1 ⊕ £188.⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | £188.00 each |
| Need More? | Request Quote |

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

UCi Series **Product Family:**

Fixed Focal Length Lens **Type:**

No **IR Cut Filter:**

Physical & Mechanical Properties

Fixed Iris Option:

26.70 Length (mm):

18 Maximum Diameter (mm):

25 Outer Diameter (mm):

13 Weight (g):

0 Maximum Rear Protrusion (mm):

25.5 Maximum Length (mm):

Optical Properties

Horizontal Field of View @ Max Sensor Format:
98.5mm - 25.3°

Field of View at Max Sensor Format:
Horizontal: 93.6mm - 25.3°
Vertical: 70.2mm - 19.1°
Diagonal: 117mm - 31.3°

Horizontal Field of View, 1/1.8" Sensor:
93.6mm - 25.3°

Horizontal Field of View, 1/2" Sensor:
83.2mm - 22.5°

Horizontal Field of View, 1/2.5" Sensor:
75.4mm - 20.5°

Horizontal Field of View, 1/3" Sensor:
62.4mm - 17.0°

Horizontal Field of View, 1/4" Sensor:
46.8mm - 12.8°

9.00 Maximum Image Circle (mm):

0.0034 Numerical Aperture NA, Object Side:

7 (5) Number of Elements (Groups):

16.00 Focal Length FL (mm):

200 - ∞ Working Distance (mm):

f/11 Aperture (f/#):

M4 MgF₂ Coating:

M4 MgF₂ Coating Specification:

10.68 Entrance Pupil Position (mm):

20.18 Object Space Principal Plane (mm):

-6.67 Image Space Principal Plane (mm):

-0.53 Maximum Distortion (%):

-29.94 Exit Pupil Position (mm):

VIS Lens Wavelength Range:

Sensor

1/2.5" Optimized Sensor Format:

1/1.8" Maximum Sensor Format:

1.85 Pixel Size (µm):

Threading & Mounting

M18 x 0.50 (Male) Filter Thread:

Mount:

Environmental & Durability Factors

-20 to +60

Storage Temperature (°C):

Type of Ruggedization:
Industrial (Fixed Aperture with Simplified Mechanics)

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

- Up to 1/1.8", C-Mount, S-Mount Lens
- Up to 12 MegaPixels, 1.85µm Pixel Size Sensors
- Instrumentation (UCi) versions of our UC Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 4mm to 35mm Focal Length

TECHSPEC® UCi Series Fixed Focal Length Lenses utilize the same optics as the TECHSPEC UC Series Lenses and feature 4K resolution. These lenses are designed for small pixels $\leq 2.2\mu\text{m}$ and offer a wide range of fixed apertures for a variety of applications. While optimized for 1/2.5" sensors, many focal length options can be used on sensors up to 1/1.8". TECHSPEC® UCi Series Fixed Focal Length Lenses are ideal for OEM applications that require small, robust, and lightweight imaging solutions.

Note: For adjustable aperture options, see our [TECHSPEC® UC Series Fixed Focal Length Lenses](#).

Edmund Optics has created a family of high-performance ultra-compact optical designs (the UC Series family) and developed 3 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the UC Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:


UC Series: Features locking cam focus and iris adjustment in an ultra-compact design and is the most adjustable version of these optical designs; they are the typical high-quality machine vision lenses.

UCi Series: Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.


UCr Series: All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.

UCw Series: Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes.


Technical Information




#33-888, 16mm, f/11 UCi Series Fixed Focal Length Lens, Distortion Plot




#33-888, 16mm, f/11 UCi Series Fixed Focal Length Lens, Relative Illumination Plot




#33-888, 16mm, f/11 UCi Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#33-888, 16mm, f/11 UCI Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 300mm Working Distance, f11



#33-888, 16mm, f/11 UCI Series Fixed Focal Length Lens, Depth of Field Plot, 300mm Working Distance, f11



#33-888, 16mm, f/11 UCI Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 750mm Working Distance, f11



#33-888, 16mm, f/11 UCI Series Fixed Focal Length Lens, Depth of Field Plot, 750mm Working Distance, f11

Compatible Cameras