

20 x 20mm Opal Checkerboard Target



Opal Checkerboard Calibration Target

Stock #12-197 **4 In Stock**

⊖ 1 ⊕ £408⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	£408.00 each
Qty 5+	£388.32 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

No **NIST Certification:**

Physical & Mechanical Properties

10 x 10 ±0.010 **Pattern Size (mm):**

20 x 20 ±0.10 **Dimensions (mm):**

1.52 ±0.10 **Thickness (mm):**

0.2 x 0.2 ±0.002 **Check Size (mm):**

Optical Properties

Coating:
Blue Chrome (reflectivity <7% @ 550nm)

Substrate:
Opal Glass

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)

Product Details

- Chrome Pattern on Dimensionally Stable Substrates (Opal and Glass)
- Optimized for Reflective Illumination Calibration of Imaging Systems
- Various Sizes for Small or Large Field of Views

Checkerboard Calibration Targets are used in the calibration of 2D industrial and machine vision cameras to detect image distortion or sensor issues to ensure measurement accuracy. These Checkerboard targets feature white ivory and opal glass substrates that remain rigid, therefore not affecting the pattern by flexure. These Checkerboard targets minimize the effect of shadowing from back reflections, making them ideal for reflective illumination calibration of imaging systems with wide field of views. These targets are available in a range of sizes to complement cameras with small or large field of views.

Note: Targets with a specification of "NIST Certification: Yes" include a calibration certificate.

Technical Information

