

TECHSPEC® 18mm Inner Single Optic Mount



TECHSPEC Multi-Element Inner Single Optic Mounts

Stock #38-753 **5 In Stock**

⊖ 1 ⊕ £32.⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	£32.80 each
Qty 5+	£31.20 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Fixed

Type:

Function:

Physical & Mechanical Properties

Construction:
Matte Black Anodized Aluminum (6061-T6)

Total Length (mm):
9.0

Clear Aperture CA (mm):
16.0

Max. Thickness of Compatible Optics (mm):
4.0

Min. Thickness of Compatible Optics (mm):
1.0

Edge Thickness of Compatible Optics (mm):
4.0

Threading & Mounting

Diameter of Compatible Optics (mm):
18.0

Thread Type:
M29 x 0.75

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

PRODUCT DETAILS

- Mounts for a Variety of Optical Component Diameters and Thicknesses
- M29 Outer Diameter Threads Allow Easy Positioning Within [Outer Tubes](#)
- One Retainer Ring and One Delrin Ring are Included
- Click [Here](#) to See How to Use the Multi-Element Tube System Components to Build an Optical System.

TECHSPEC® Multi-Element Inner Single Optic Mounts are designed to mount a variety of optical components. The mounts support optical diameters from 5mm to 25.4mm, and edge thicknesses of 4mm to 17mm. With M29 x 0.75 outer diameter threads, these mounts can be easily positioned along the optical axis of our TECHSPEC® Multi-Element Outer Tubes. TECHSPEC® Multi-Element Inner Single Optic Mounts include one Delrin ring to ensure secure clamping force between the retainer ring and optic without damaging the optic.

Note: Our specially designed ME Spanner Wrench ([#13-567](#)) is highly recommended to move Inner Single Optic Mounts back and forth smoothly utilizing a combined metric and English graduated scale. The hollow design enables transmission of output beam while adjusting lens position. Non-scaled ME Spanner Wrench ([#11-046](#)) is also available.