

1mW, 808nm Alignment Laser Diode (Recertified 05-P)



Red and IR Alignment Laser Diode

Stock **#19-449-RCD-05P** RECERTIFIED **1 In Stock**

-

1

+

£100⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£100.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads



SPECIFICATIONS

General

IIIb

Laser Class - CDRH:

Physical & Mechanical Properties

Length (mm):

36.00	
Optical Properties	
808.00	Wavelength (nm):
±5	Wavelength Tolerance (nm):
2 x 4 typical	Beam Diameter (mm):
<5.0	Beam Divergence (mrad):
infrared	Color:
Electrical	
1	Output Power (mW):
0 - 10	Modulation Frequency (kHz):
Hardware & Interface Connectivity	
5	Operating Voltage (V):
Power Supply: Power Supply Required and Sold Separately. USA: #73-818 Europe: #73-818 Japan: #13-640 Korea: #33-770 China: #73-818	
Environmental & Durability Factors	
-10 to 50	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Focus Adjustable
 - TTL Mbdulation up to 10kHz
 - 635nm, 780nm, 808nm, 850nm, and 980nm Wavelength Options
- Red and IR Alignment Laser Diodes are available in output powers from 1 to 100mW at 635nm, 780nm, 808nm, 850nm, and 980nm wavelengths. These low cost laser diode modules combine drive electronics and beam collimating optics, making them ideal for OEM integration applications. Red and IR Alignment Laser Diodes feature TTL Mbdulation up to 10kHz and are best utilized in alignment applications or systems with simple detectors.
- Note:** Power supply and mounting bracket are sold separately.