

2 - 12um HgCdTe Photovoltaic Multi-Junction Detector Module, LabM-1-10.6



2 - 12um HgCdTe Photovoltaic Multi-Junction Detector Module, LabM-1-10.6

Stock **#90-458** NEW **2 In Stock**

£2,364.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£2,364.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

IR Photovoltaic Detection Module

Type:

Software:
 Software Package, Requires Controller ([#90-469](#))
[SmartManager](#)
[Python Library](#)
[Documentation](#)

Model Number:

LabM-I-10.6

Manufacturer:

Vigo Photonics

Physical & Mechanical Properties

Weight (g):

310

Size of Active Area (mm):

1.00 x 1.00

Dimensions (mm):

88.5 x 40.0 x 45.6

Active Area (mm):

1.00 x 1.00

Optical Properties

Spectral Response (nm):

2000 - 12000

Acceptance Angle (°):

36

Electrical

Bandwidth (MHz):

Up to 120 MHz

Hardware & Interface Connectivity

Power Supply:

Power Supply Required(#90-469) and Sold Separately

Environmental & Durability Factors

Operating Temperature (°C):

+10 to +30

Storage Temperature (°C):

-20 to +85

Additional Info

Included Components:

(1) SMA-BNC Cable, (1) LEMO-DB9 Cable

Regulatory Compliance

RoHS 2015:

[Exempt](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Compliant](#)

Product Details

- Built-In Preamplifiers and TEC Control Options
- Mid and Long-Wave Infrared (MMIR/LWIR) Spectral Ranges
- Evaluation Kits and Digital Interfaces for Simplified Setup and Data Acquisition

Vigo Photonics Infrared Detector Modules offer solutions that combine advanced IR detector technology with integrated electronics for simplified system integration. These compact modules feature options ranging from uncooled micro-size designs to multi-stage TE-cooled laboratory systems with programmable preamplifiers. Evaluation kits, digital interfaces, and built-in TEC controllers ensure fast setup and reliable operation across diverse environments. Vigo Photonics Infrared Detector Modules are available in configurations optimized for mid-wave and long-wave infrared, with spectral coverage from 2 to 12µm. Ideal for spectroscopy, gas sensing, industrial monitoring, and defense applications, these modules deliver high performance in flexible, ready-to-use packages.