

Screw Drive Fiber Alignment Mount



2-Axis Fiber Alignment Mount w/ Standard Kinematic Movement, #55-476

Stock **#55-476** **3 In Stock**

⊖ 1 ⊕ £381⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£381.60 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Adjustable - Linear (XY) **Type:**

Fiber Connector **Type of Optics:**

Physical & Mechanical Properties

Black Anodized Aluminum **Construction:**

Linear Travel (mm):

±1.5

Electrical

FC

Fiber Connection:

Hardware & Interface Connectivity

Lead Screw

Type of Drive:

Threading & Mounting

M4 x0.7

Compatible Post:

Regulatory Compliance

[Exempt](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Contains SVHC\(s\)](#)

Reach 247:

Product Details

[Posts](#) and [Post Holders](#) are required for mounting to a breadboard.

- FC Fiber Connection
- Two Axis Linear Movement for Precise Fiber Alignment
- Optional Kinematic Tilt Version
- [Posts](#) and [Post Holders](#) Required for Mounting

Fiber Optic Alignment Mounts can translate optical fibers terminating in an FC connection. Useful for telecom positioning and for aligning FC Fiber Optic Patchcords, they feature ±1.5mm travel in both the X and Y-axis. The Differential Micrometer models feature 2.5 micron resolution while the kinematic version ([#55-478](#)) provides an additional ±2° tilt adjustment on each axis.

Note: [Posts](#) and [Post Holders](#) are required for mounting to a breadboard.

Technical Information

