

TECHSPEC[®] 20.0mm Diameter x 20.0mm FL, 405nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex (PCX) Lenses



Stock **#88-970** 3-4 DAYS

[Other Coating Options](#)

-

1

+

£46.75

ADD TO CART

Qty 1-9
£46.75
Qty 10+
£42.07
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.025

Effective Focal Length EFL (mm): 20.00 @ 587.6nm
Back Focal Length BFL (mm): 17.42
Coating: Laser V-Coat (405nm)
Coating Specification: R _{abs} <0.25% @ 405nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 4.60 ±0.10
Edge Thickness ET (mm): 1.00
Radius R₁ (mm): 15.70
Clear Aperture CA (mm): 19
f/#: 1.00
Numerical Aperture NA: 0.50
Design Wavelength DWL (nm): 405
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Damage Threshold, By Design: ☐ 3 J/cm ² @ 405nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant