



TECHSPEC<sup>®</sup> 20 x 20mm, 400 - 750nm Broadband  $\lambda/10$  Mirror



Stock **#29-916** 20+ In Stock

-

1

+

£88<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | £88.00 each                   |
| Qty 6-25       | £70.40 each                   |
| Qty 26-49      | £66.00 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:  
Flat Mirror

Physical & Mechanical Properties

Thickness (mm):

|                                                                                         |                                                       |
|-----------------------------------------------------------------------------------------|-------------------------------------------------------|
| 3.00 ±0.20                                                                              |                                                       |
| 20.00 x 20.00 +0.00/-0.20                                                               | Dimensions (mm):                                      |
| Commercial Polish                                                                       | Back Surface:                                         |
| 90                                                                                      | Clear Aperture (%):                                   |
| Ground, 0.5mm max bevel                                                                 | Edges:                                                |
| <0.5                                                                                    | Parallelism (arcmin):                                 |
| 30                                                                                      | Parallelism (arcsec):                                 |
| Optical Properties                                                                      |                                                       |
| Dielectric                                                                              | Coating Type:                                         |
| Dielectric Mirror (400-750nm)                                                           | Coating:                                              |
| $\lambda/10$                                                                            | Surface Flatness (P-V):                               |
| 400 - 750                                                                               | Wavelength Range (nm):                                |
| <a href="#">Fused Silica</a> (Corning 7980)                                             | Substrate: <input type="checkbox"/>                   |
| 0-45                                                                                    | Angle of Incidence (°):                               |
| R <sub>avg</sub> >98% @400 - 750nm (0 - 45°)<br>R <sub>avg</sub> >99% @400 - 750nm (0°) | Coating Specification:                                |
| 20-10                                                                                   | Surface Quality:                                      |
| 0.5 J/cm² @532nm, 20ns, 20Hz                                                            | Damage Threshold, Reference: <input type="checkbox"/> |
| Regulatory Compliance                                                                   |                                                       |
| <a href="#">View</a>                                                                    | Certificate of Conformance:                           |

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Enhanced Reflectivity and LIDT over Metallic Coatings
- Average Reflectivity >99% Over Broad UV, Visible, and NIR Wavelengths
- Designed for all Polarization States from 0 – 45° AOI

TECHSPEC® Broadband Dielectric  $\lambda/10$  Mirrors are ideal for beam steering or reflection applications utilizing multiple laser sources. These mirrors feature greater than 99% reflection, significantly better than metal-coated mirrors, and increase system performance by minimizing energy loss. The highly durable fused silica substrate offers a low thermal expansion coefficient and a high abrasion resistance. TECHSPEC® Broadband Dielectric  $\lambda/10$  Mirrors are designed for applications from the UV to the near-infrared spectra.

## Technical Information

