

20 x 20mm, 800µm Pitch, 0.3° Divergence, Cyl. Microlens Array



Stock #23-873 3-4 DAYS

-

1

+

£454.75

ADD TO CART

Qty 1-10
£454.75
Qty 11+
£409.70
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
173.50 @ 1064nm

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Coating:
Uncoated

Type:

Lens Array (One Sided)
Wavelength Range (nm): 200 - 2200
Dimensional Tolerance (mm): ±0.1
Dimensions (mm): 20.0 x 20.0
Divergence Angle (°): 0.3 (Full Width)
Pitch (µm): 800
Radius R (mm): 78.000
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View