

[See all 215 Products in Family](#)

TECHSPEC®

20mm Dia., 0.50 Numerical Aperture, 350-700nm Coated, Inked, High Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#16-955-INK** [CONTACT US](#)

[Other Coating Options](#)

⊖ 1 ⊕ £311²⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£311.20 each
Qty 6-10	£280.00 each
Qty 11-25	£255.20 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

20.00 ±0.025	Diameter (mm):
<3	Centering (arcmin):
18.00	Clear Aperture CA (mm):
7.23	Edge Thickness ET (mm):
11.20 ±0.10	Center Thickness CT (mm):
Protective as needed	Bevel:
Plano	Shape of Back Surface:
Optical Properties	
20.00 @ 587.6nm	Effective Focal Length EFL (mm):
0.50	Numerical Aperture NA:
13.31	Back Focal Length BFL (mm):
N-SF5	Substrate: <input type="checkbox"/>
0.4λ	Asphere Figure Error, RMS @ 632.8nm:
VIS-EXT+ (350-700nm)	Coating:
Coating Specification: R _{avg} <0.5% @ 350 - 700nm @ ±30° AOI R _{abs} <1.5% @ 350 - 700nm @ ±30° AOI	
40-20	Surface Quality:
1.00	f#:
350 - 700	Wavelength Range (nm):
Infinite	Conjugate Distance:

Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Improved Versions of Our Aspheric Lenses
- Precision Grade Aspheric Surfaces
- High Numerical Apertures to Maximize Throughput

TECHSPEC® Precision Aspheric Lenses are CNC polished aspheric lenses that feature a 0.4λ RMS aspheric figure error. The precision aspheric figure error makes these lenses ideal for applications that require spherical aberration correction, including imaging and laser focusing applications. These aspheric lenses can also be used to replace multiple spherical elements in optical assemblies to reduce weight and cost. TECHSPEC Precision Aspheric Lenses are available with diameters from 6 to 50mm and high numerical apertures to maximize light throughput.

Compatible Mounts