

TECHSPEC® 20mm Dia., 0.56 NA, 900-1700nm Coated, NIR Aspheric Lens



TECHSPEC® Near-Infrared (NIR) Aspheric Lenses

Stock **#16-295** 3-4 DAYS

[Other Coating Options](#)



1



£216.75

ADD TO CART

Qty 1-5

£216.75

Qty 6+

£173.40

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
20.00 +0.00/-0.10

Effective Focal Length EFL (mm):
17.99 @ 780nm

Numerical Aperture NA:

0.56
Back Focal Length BFL (mm): 14.00
Substrate: S-LAH64
Aspheric Design Wavelength (nm): 780
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: SWIR+ (900-1700nm)
Coating Specification: R _{avg} < 0.5% @ 900 - 1700nm @ 0° ±30° AOI R _{abs} < 1% @ 900 - 1700nm @ 0° ±30° AOI
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 18
Edge Thickness ET (mm): 3.37
Center Thickness CT (mm): 7.10 ±0.10
f/#: 0.90
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 900 - 1700
Conjugate Distance: Infinite
Power (diopters): 55.59

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View