

[See all 423 Products in Family](#)

TECHSPEC[®] 2.0mm Dia. x 2.0mm FL, NIR I Coated, Plano-Convex Lens



Stock **#45-956** [CONTACT US](#)

☐ [Other Coating Options](#)

-

1

+

£70⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	£70.00 each
Qty 10-24	£62.80 each
Qty 25-49	£56.40 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties

2.00 +0.0/-0.025	Diameter (mm):
30-45, typical	Centering (arcmin):
0.80 ±0.05	Center Thickness CT (mm):
0.48	Edge Thickness ET (mm):
1.5	Clear Aperture CA (mm):
Protective as needed	Bevel:

Optical Properties	
2.00 @ 587.6nm	Effective Focal Length EFL (mm):
1.57	Back Focal Length BFL (mm):
NIR I (600-1050nm)	Coating:
R _{avg} ≤0.5% @ 600 - 1050nm	Coating Specification:
N-LASF9	Substrate: □
20-10	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
±1	Focal Length Tolerance (%):
1.70	Radius R ₁ (mm):
1	f#:
0.50	Numerical Aperture NA:
600 - 1050	Wavelength Range (nm):
7 J/cm ² @ 1064nm, 10ns	Damage Threshold, By Design: □

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details



- AR Coated to Provide <0.5% Reflectance per Surface for 600 - 1050nm
- Designed for 0° Angle of Incidence
- Various PCX Coating Options: [Uncoated](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR II](#), [VIS-EXT](#), and [YAG-BBAR](#)

TECHSPEC® NIR I Coated Plano-Convex (PCX) Lenses have a positive focal length, making them ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. TECHSPEC® NIR I Coated Plano-Convex (PCX) Lenses are available in a wide variety of diameters and focal lengths. Identical designs of these PCX lenses are also offered [uncoated](#) or with broadband anti-reflective (BBAR) coatings, which include [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR II](#), [VIS-EXT](#), and [YAG-BBAR](#).

Technical Information



N-BK7																									
Uncoated N-BK7 Typical Transmission <table border="1"><caption>Uncoated N-BK7 Typical Transmission Data (Approximate)</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>400</td><td>92</td></tr><tr><td>600</td><td>93</td></tr><tr><td>800</td><td>93</td></tr><tr><td>1000</td><td>93</td></tr><tr><td>1200</td><td>93</td></tr><tr><td>1400</td><td>92</td></tr><tr><td>1600</td><td>93</td></tr><tr><td>1800</td><td>92</td></tr><tr><td>2000</td><td>91</td></tr><tr><td>2200</td><td>88</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	70	400	92	600	93	800	93	1000	93	1200	93	1400	92	1600	93	1800	92	2000	91	2200	88	Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																								
200	70																								
400	92																								
600	93																								
800	93																								
1000	93																								
1200	93																								
1400	92																								
1600	93																								
1800	92																								
2000	91																								
2200	88																								
N-BK7 with MgF₂ Coating Typical Transmission <table border="1"><caption>N-BK7 with MgF₂ Coating Typical Transmission Data (Approximate)</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>400</td><td>95</td></tr><tr><td>600</td><td>98</td></tr><tr><td>800</td><td>95</td></tr><tr><td>1000</td><td>94</td></tr><tr><td>1200</td><td>93</td></tr><tr><td>1400</td><td>93</td></tr><tr><td>1600</td><td>93</td></tr><tr><td>1800</td><td>92</td></tr><tr><td>2000</td><td>91</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	70	400	95	600	98	800	95	1000	94	1200	93	1400	93	1600	93	1800	92	2000	91	2200	90	Typical transmission of a 3mm thick N-BK7 window with MgF₂ (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$ (N-BK7) Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Wavelength (nm)	Transmission T (%)																								
200	70																								
400	95																								
600	98																								
800	95																								
1000	94																								
1200	93																								
1400	93																								
1600	93																								
1800	92																								
2000	91																								
2200	90																								
N-BK7 with VIS-EXT Coating Typical Transmission <table border="1"><caption>N-BK7 with VIS-EXT Coating Typical Transmission Data (Approximate)</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>350</td><td>95</td></tr><tr><td>400</td><td>98</td></tr><tr><td>600</td><td>98</td></tr><tr><td>700</td><td>98</td></tr><tr><td>800</td><td>95</td></tr><tr><td>1000</td><td>85</td></tr><tr><td>1200</td><td>78</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	70	350	95	400	98	600	98	700	98	800	95	1000	85	1200	78	Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data						
Wavelength (nm)	Transmission T (%)																								
200	70																								
350	95																								
400	98																								
600	98																								
700	98																								
800	95																								
1000	85																								
1200	78																								
N-BK7 with VIS-NIR Coating Typical Transmission <table border="1"><caption>N-BK7 with VIS-NIR Coating Typical Transmission Data (Approximate)</caption><thead><tr><th>Wavelength (nm)</th><th>Transmission T (%)</th></tr></thead><tbody><tr><td>200</td><td>75</td></tr><tr><td>400</td><td>98</td></tr><tr><td>600</td><td>98</td></tr><tr><td>800</td><td>98</td></tr><tr><td>870</td><td>98</td></tr><tr><td>1000</td><td>95</td></tr><tr><td>1200</td><td>80</td></tr></tbody></table>	Wavelength (nm)	Transmission T (%)	200	75	400	98	600	98	800	98	870	98	1000	95	1200	80	Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% @ 880\text{nm}$ $R_{avg} \leq 1.25\% @ 400 - 870\text{nm}$ $R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data								
Wavelength (nm)	Transmission T (%)																								
200	75																								
400	98																								
600	98																								
800	98																								
870	98																								
1000	95																								
1200	80																								

	Click Here to Download Data
N-BK7 with VIS 0° Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.4\%$ @ 425 - 675nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with YAG-BBAR Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\%$ @ 532nm $R_{abs} \leq 0.25\%$ @ 1064nm $R_{avg} \leq 1.0\%$ @ 500 - 1100nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with NIR I Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\%$ @ 600 - 1050nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with NIR II Coating Typical Transmission 	Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.5\%$ @ 750 - 800nm $R_{abs} \leq 1.0\%$ @ 800 - 1550nm $R_{avg} \leq 0.7\%$ @ 750 - 1550nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data

