

TECHSPEC® 22 x 22mm Protected Aluminum, λ/4 Mirror



Stock **#33-510** ☐ In Stock

1 **£40.38**

ADD TO CART

Qty 1-5
£40.38
Qty 6+
£32.30
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate: ☐
[BOROFLOAT®](#)

Back Surface:
Ground

Surface Quality: 60-40
Dimensions (mm): 22.0 x 22.0
Dimensional Tolerance (mm): +0/-0.5
Coating Specification: R _{avg} >85% @400 - 700nm R _{avg} >90% @400 - 2000nm
Coating: Protected Aluminum (400-2000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%) : 85
Edges: Fine Ground
Thickness (mm): 5.00 +0.5/-0
Type: Flat Mirror
Wavelength Range (μm): 0.4 - 2.0
Wavelength Range (nm): 400 - 2000
Length (mm): 22.00
Width (mm): 22.00
Damage Threshold, Reference:  0.3 J/cm ² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View