

[See all 2 Products in Family](#)

## 230V, with UK Cord, DC950HK Illuminator

See More by [Dolan-Jenner](#)



230V, with UK Cord, DC950HK Illuminator, #62-006

Stock **#62-006** [CONTACT US](#)

⊖ 1 ⊕ £956<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-5	£956.00 each
Qty 6+	£860.40 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

### General

150 WEKE Quartz Halogen **Type:**

0.5VDC or 8 bit digital optional **Intensity Control Option:**

**Lamp Lifetime (hours):**

200 - 10,000

**Type of Illumination:**

Fiber Optic Illuminator, Incandescent

**Compatible Light Guide Adapter:**

25mm Interface: **MX** (Preferred), **SX** for semi-rigid light guides or hybrid light guides

**Manufacturer:**

Dolan-Jenner

**Illumination Mode:**

Constant

### Physical & Mechanical Properties

**Height (inches):**

4.5

**Length (inches):**

9.5

**Weight (lbs):**

11.5

**Width (inches):**

7.25

**Construction:**

Aluminum

### Optical Properties

**Color:**

White

### Electrical

**Voltage (V):**

230

**Output Power (Lumens):**

1800.00

**Ripple (%):**

0.4% or better

### Hardware & Interface Connectivity

**Power Supply:**

± 0.5% or better regulation

### Environmental & Durability Factors

**Operating Temperature (°C):**

+5 to +40

**Operating Humidity:**

0% to 80% non-condensing

### Regulatory Compliance

**Reach 174:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)


## Product Details

Requires Dolan-Jenner SX Fiber Optic [Adapters](#).

- DC-Regulated Power Supply Less Than 0.5%
- Low Output Power Ripple Less Than 0.4%
- Remote Intensity Control from 0-5V DC Analog
- 200 to 10,000 Hours Lamp Life

The DC-950H is a cost effective 150W quartz halogen light source designed specifically for machine vision lighting. This light source has a compact footprint, making it a great addition to any lab or workspace. In addition to the 0 to 100% intensity control and heat absorbing filter, the basic model features less than 0.4% variation in the power output as compared to typical 2% variance in non-regulated or AC-regulated illuminators. Built-in remote interface permits precise intensity control of output power via 0-5VDC analog input or an 8 bit digital interface. Dolan-Jenner SX Fiber Optic [Adapters](#) are sold separately and required for use with a light guide.

## Technical Information



Dolan-Jenner Illuminator

