

TECHSPEC[®] 20mm Dia. x 35mm FL, VIS-NIR Coated, Achromatic Lens



Stock #49-349 3-4 DAYS

[Other Coating Options](#)

-

1

+

£88.40

ADD TO CART

Qty 1-5

£88.40

Qty 6+

£70.76

Volume Pricing

[Request Quote](#)

ⓘ

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.025

Effective Focal Length EFL (mm):

35.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 29.90
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 19.00
Centering (arcmin): <1
Center Thickness CT (mm): 9.09 ±0.20
Center Thickness CT 1 (mm): 7.33 ±0.10
Center Thickness CT 2 (mm): 1.76 ±0.10
Radius R ₁ (mm): 24.24
Radius R ₂ (mm): -15.96
Radius R ₃ (mm): -139.78
Edge Thickness ET (mm): 6.57
Substrate:  S-BAH11 / N-SF10
Surface Quality: 40-20
f/#: 1.75
Numerical Aperture NA: 0.29
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View