

[« See all 8 Products in Family](#)
[All Products](#) / [Optics](#) / [Polarization Optics](#) / [Linear Polarizers](#)
[/ Wire Grid \(Reflective\) Polarizers](#) / [High Contrast IR Wire Grid Polarizers](#)

25 x 25mm, 7-15 μ m, High Contrast IR Wire Grid Polarizer


 Stock #88-249 **3 In Stock**

 - 1 + **£1,400^{.00}**
[ADD TO CART](#)

Volume Pricing	
Qty	£1,400.00
1+	each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

- STEP:step
- Curve:pdf
- PDF Drawing:pdf
- IGES:igs
- eDrawing:eprt
- EO Spec Sheet
- [Download All](#)

General

Type: Linear Polarizer

Physical & Mechanical Properties

Length (mm): 25.00

Dimensions (mm): 25.0 x 25.0 ±0.4

Thickness (mm): 0.70 ±0.07

Construction: Wire Grid

Alignment Tolerance (°): ±2

Width (mm): 25.00

Microwire Material: Aluminum

Optical Properties

Angle of Incidence (°): 0 ±20

Extinction Ratio: 7000:1 @ 8 μ m, 7000:1 @ 10.6 μ m, 7000:1 @ 12 μ m

Substrate: ^① Silicon (Si)

Transmission (%): T_p >85% @ 8.0 μ m
T_p >81% @ 10.6 μ m
T_p >75% @ 12.0 μ m

Wavelength Range (nm): 8000 - 12000

Damage Threshold, By Design: ^① 100 kW/cm² Blocking Direction
10 kW/cm² Transmission Direction @ 3.3 μ m, 7ns, 25kHz, 150 μ m Spot Size

Material Properties

Thermal Expansion: 2.6 x 10⁻⁷/°C

Environmental & Durability Factors

Operating Temperature (°C): Up to 200

Regulatory Compliance

RoHS 2015: **Compliant**

Reach 224: **Compliant**

Certificate of Conformance: **View**

Product Details

Due to the wire grid being exposed, special care should be taken when handling to prevent damage to the polarizer.

- AR Coated for Superior Transmission
- High Heat Resistance with Low Thermal Expansion
- Feature Wide Angle of Incidence Range without Performance Loss

High Contrast IR Wire Grid Polarizers are ideal for broadband infrared applications that require high transmission and contrast, including spectroscopy, remote sensing, thermal imaging, or astronomy. Aluminum Microwire versions consist of a silicon substrate and are available in both 3–5 μm and 7–12 μm options. These polarizers will have up to 7000:1 contrast at their specified wavelengths, and a temperature resistance of up to 200°C. Gold Microwire versions consist of a silicon substrate with gold microwires and feature superior contrast of at least 10,000:1 @ 3.4 μm . Due to their unique construction, these polarizers have a substantial temperature resistance of up to 500°C making them perfect even for the most demanding applications. High Contrast IR Wire Grid Polarizers allow the angle of incidence to vary from $\pm 20^\circ$ for the aluminum microwire versions or $\pm 25^\circ$ for the gold without displaying performance loss.

Note: Due to the exposed wire grid, special care should be taken when handling to prevent damage to the polarizer. The wire grid surface should never be touched directly, and parts should be handled by the edges only, with light pressure, using gloves. The glass side can be gently cleaned using isopropyl alcohol, but the wire grid side should only be cleaned using compressed air.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Related Products



#11-147 - 50mm Diameter, T-Mount Polarizer Holder
£181.60

Qty



#12-837 - 25.0mm Square Polarizer Adapter, 50.0mm Outer Diameter
£31.20

Qty

Resources


Media Type

APPLICATION NOTE
Introduction to Polarization


SCIENTIFIC PAPER

VIDEO
Infrared Light

- Application Note
- Scientific Paper
- Video
- Glossary
- Technical Tool
- FAQ



Advantages of
using
engineered
chalcogenide...



GLOSSARY

Short Wave
Infrared
(SWIR)

TECHNICAL TOOL

Laser-Cut
Polymer
Polarizer and
Retarder...

APPLICATION NOTE

Advantages of
Using
Meniscus
Lenses in...

[View More](#)