

TECHSPEC® 25.0mm 248nm 45°, Excimer Laser Line Mirror



TECHSPEC Excimer Laser Line Mirrors

Stock **#47-985** 3-4 DAYS



1



£206.55

ADD TO CART

Qty 1-5

£206.55

Qty 6+

£181.90

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):

<3
Clear Aperture (%)>90
Back Surface:Ground
Reflection at DWL (%)99
Coating Specification:R_{abs} >99% @ 248nm
Surface Flatness (P-V):λ/10
Coating Type:Dielectric
Coating:Dielectric Mirror (248nm)
Design Wavelength DWL (nm):248
Diameter (mm):25.00 +0.0/-0.2
Thickness (mm):6.00 ±0.2
Angle of Incidence (°):45
Substrate: Fused Silica (Coming 7980)
Damage Threshold, Reference: 1.5 J/cm² @ 10ns by design

Regulatory Compliance

RoHS 2015:Compliant
Reach 209:Compliant
Certificate of Conformance:View