

2.0" x 2.0", FL -0.85", Aspheric Fresnel Lens



Aspherically Contoured Fresnel Lenses

Stock **#46-394** **5 In Stock**

-

1

+

£31²⁰

ADD TO CART

Volume Pricing	
Qty 1-10	£31.20 each
Qty 11-49	£28.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

Fresnel Lens

Physical & Mechanical Properties

0.06	Center Thickness CT (inches):
±0.05	Dimensional Tolerance (inches):
2.0 x 2.0	Dimensions (inches):
50.8 x 50.8	Dimensions (mm):
1.3	Effective Diameter (inches):
±40	Thickness Tolerance (%):
Optical Properties	
-21.59	Effective Focal Length EFL (mm):
Acrylic	Substrate: ☐
Uncoated	Coating:
400 - 1100	Wavelength Range (nm):
-0.85	Effective Focal Length EFL (inches):
200.00	Groove Density (grooves/inch):
1.49	Index of Refraction (n _d):
85 (Typical)	Transmission (%):
Environmental & Durability Factors	
≤80	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:

PRODUCT DETAILS

- Negative Focal Length
- Acrylic Substrate
- Square and Rectangular Options

A Fresnel lens replaces the curved surface of a conventional lens with a series of concentric grooves, molded into the surface of a thin, lightweight plastic sheet. The grooves act as individual refracting surfaces, like tiny prisms when viewed in cross section, bending parallel rays in a very close approximation to a common focal length. Because the lens is thin, very little light is lost by absorption. Fresnel lenses are a compromise between efficiency and image quality. High groove density allows higher quality images, while low groove density yields better efficiency (as needed in light gathering applications). In infinite conjugate systems, the grooved side of the lens should face the longer conjugate.

Fresnel lenses are most often used in light gathering applications, such as condenser systems or emitter/detector setups. Fresnel lenses can also be used as magnifiers or projection lenses; however, due to the high level of distortion, this is not recommended.

TECHNICAL INFORMATION

