

2.0X, High Resolution Inline Telecentric Lens



Stock #65-028 **1 In Stock**

- 1 + £3,028.⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£3,028.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Product Family:
High Res In-Line Illumination C-Mnt Telecentric Lenses

Note:
Magnification Tolerance %: ±3

Type:
Telecentric Lens

Compatible Light Guide/Source:
1/4" (0.312")

Type of Illumination:

Physical & Mechanical Properties

250.00 Length (mm):

54 Maximum Diameter (mm):

Optical Properties

4.4mm Horizontal Field of View, 2/3" Sensor:

11.00 Maximum Image Circle (mm):

0.13 Numerical Aperture NA, Object Side:

5.70 Resolving Power, Image Space (μm): ± 1.00 Working Distance Tolerance (mm):

2X Primary Magnification PMAG:

2.00 Telecentric Lens Magnification:

100.00 Working Distance (mm):

f/8 - Closed Aperture (f/#):

 ≤ 0.05 Distortion (%):

2X Magnification:

VIS Lens Wavelength Range:

Sensor

2/3" Maximum Sensor Format:

2.60 Pixel Size (μm):**Threading & Mounting**

N/A Filter Thread:

C-Mount Mount:

Regulatory Compliance[View](#) Certificate of Conformance:**Product Details**

- Designed for High Resolution Imaging
- In-line Illumination Port (0.312" Ferrule)
- 2/3" Max. Sensor Format

This line of high resolution telecentrics was designed to allow of in-line illumination. This make them ideal for applications that need intense and direct illumination. The coaxial port accepts 1/4" fiber bundles with a 0.312" ferrule diameter, which readily connects to our wide selection of light guides and illuminators.

The lenses feature a standard C-Mount threading to connect to the most common 2/3" and smaller machine vision cameras. Designed to have $\pm 0.05\%$ distortion, these lenses are perfect for challenging measurement applications.