

22.2mm Aperture UV/VIS Fiber Optic Collimator, FC



Stock **#17-569** **5 In Stock**

-

1

+

£466⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-10	£466.40 each
Qty 11-24	£413.60 each
Qty 25-49	£387.20 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Fiber Collimator	Type:
0.22	Compatible Fiber NA:
	Housing Material:

Stainless Steel	
Note: Compatible with #17-573 , #17-574 , & #17-575 Refocusing Assemblies	
Physical & Mechanical Properties	
28.58	Diameter (mm):
22.2	Aperture Size:
52.83	Length (mm):
Optical Properties	
Fused Silica (Corning 7980)	Substrate: ☐
190 - 1250	Wavelength Range (nm):
800 - 1000	Fiber Diameter (µm):
38.00	Focal Length FL (mm):
Hardware & Interface Connectivity	
FC	Connector:
Environmental & Durability Factors	
-40 to 100	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:



Product Details

- Can Be Coupled to Standard 0.22 NAFiber Optic Cables
- Options Available for UV-VIS or VIS-NIR
- Multiple Focal Length or Aperture Options


Focusable Collimators consist of two separate components: a fiber optic collimator and a fiber optic refocusing assembly. The fiber optic collimator utilizes a PCX lens positioned at the focal length from the optical fiber tip. These collimators are available with FC or SMA threads, and easily couple to standard 0.22 NA fiber optic cables. Focusable Collimators expand the beam and decrease the divergence by the ratio of the fiber core diameter to the collimator aperture. Fiber optic refocusing assemblies mount directly to the fiber optic collimator and allow for optimal focus at a given distance.



Technical Information



Fiber with 10mm Aperture Fiber Optic Collimator and Refocusing Assembly



A 10mm Aperture Refocusing Assembly can then be directly threaded onto the 10mm Aperture Fiber Optic Collimator.

Collimator Description	Stock Number	Compatible Refocusing Assembly
4mm Aperture UV/MS Fiber Optic Collimator, FC	#88-189	No Compatible Refocusing Assemblies
4mm Aperture UV/MS Fiber Optic Collimator, SMA	#88-173	No Compatible Refocusing Assemblies
4mm Aperture VIS/NIR Fiber Optic Collimator, FC	#88-188	No Compatible Refocusing Assemblies
4mm Aperture VIS/NIR Fiber Optic Collimator, SMA	#88-172	No Compatible Refocusing Assemblies
10mm Aperture UV/MS Fiber Optic Collimator, FC	#88-191	#88-182, #88-183, #88-184, #88-185, #88-186, & #88-187
10mm Aperture UV/MS Fiber Optic Collimator, SMA	#88-181	#88-182, #88-183, #88-184, #88-185, #88-186, & #88-187
10mm Aperture VIS/NIR Fiber Optic Collimator, FC	#88-190	#88-182, #88-183, #88-184, #88-185, #88-186, & #88-187
10mm Aperture VIS/NIR Fiber Optic Collimator, SMA	#88-180	#88-182, #88-183, #88-184, #88-185, #88-186, & #88-187