

**TECHSPEC® 22mm Max Aperture AR Motorizable Iris**



High Performance Motorizable Iris



Stock #24-204 **20+ In Stock**

− 1 + £123<sup>20</sup>

**ADD TO CART**

Volume Pricing

Qty 1-4	£123.20 each
Qty 5+	£109.12 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Unmounted **Type:**

**Physical & Mechanical Properties**

22.0 **Maximum Aperture (mm):**

33.0 **Outer Diameter (mm):**

**Construction:**  
Brass-Spring Steel, Anti-Reflection (AR) Leaves

14 **Number of Leaves:**

5.50 **Thickness (mm):**

30 **Pitch Diameter (mm):**

## Optical Properties

1.4 **Minimum Aperture (mm):**

## Regulatory Compliance

**RoHS 2015:**  
[Exempt](#)

**Certificate of Conformance:**  
[View](#)

**Reach 247:**  
[Contains SVHC\(s\)](#)

## Product Details

- Fast Accurate Repeatable Motion
- Dual Control Gear and Lever Mechanics
- Removable Pin for OEM Integration
- Anti-Reflection (AR) Leaves Available
- Iris Diaphragm Mounts and Motor Sold Separately

TECHSPEC® High Performance Motorizable Irises are designed for integration into custom applications and for use in a lab environment. These irises include two methods for controlling the aperture size: one by a standard pin which enables standard angular deviation and the other that duplicates the movement of the pin by replicating the teeth of a spur gear on the inner housing of the iris. This feature allows for custom motion control in conjunction with a compatible spur gear. TECHSPEC® High Performance Motorizable Irises maintain fast, accurate, and repeatable movement to any location through the iris's range of motion. The 7mm, 12mm, 22mm, 28mm, and 34mm Max Aperture configurations are also available with Anti-Reflection (AR) Leaves.

## Technical Information

