

2/3" Format C-Mount Fisheye Lens 1.8mm FL



Stock **#62-274** [CONTACT US](#)

-

1

+

£760^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£760.00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Fisheye Imaging Lenses	Product Family:
Fixed Focal Length Lens	Type:
Fisheye	Special Type of Lens:
Physical & Mechanical Properties	
Variable	Iris Option:

52.10	Length (mm):
56.5	Maximum Diameter (mm):
56.5	Outer Diameter (mm):

135.00	Weight (g):
--------	-------------

Optical Properties

185°	Horizontal Field of View, 1/2" Sensor:
------	--

11.00	Maximum Image Circle (mm):
-------	----------------------------

1.80	Focal Length FL (mm):
------	-----------------------

100 - ∞	Working Distance (mm):
---------	------------------------

f/1.4 - f/16	Aperture (f/#):
--------------	-----------------

VIS	Lens Wavelength Range:
-----	------------------------

Sensor

2/3"	Maximum Sensor Format:
------	------------------------

3.45	Pixel Size (µm):
------	------------------

Threading & Mounting

N/A	Filter Thread:
-----	----------------

C-Mount	Mount:
---------	--------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Contains SVHC(s)	Reach 233:
----------------------------------	------------

Product Details

- 2/3", C-Mount Lens
- Wide Field of View (185°) for Fisheye Images
- Lockable Iris Control and Fixed Focus
- 1.8mm Focal Length

Fisheye Imaging Lenses are designed to support MegaPixel resolution cameras across a 185° field of view. Their large depth of field eliminates the need for focus adjustment and allows the lenses to be sharply focused between 100mm and infinity. A lockable iris adjustment enables control over the exposure without changing integration time and stays locked in place to prevent accidental alteration. Fisheye Imaging Lenses are excellent for space-constrained applications where large fields of view are required at short working distances. These lenses have a 1.8mm focal length. *FOV for 1/2" format sensor.