

248nm CWL, 10nm FWHM, 50mm Mounted Diameter



Stock #67-873 3-4 DAYS

⊖ 1 ⊕ **£464.10**

ADD TO CART

Qty 1-9

£464.10

Qty 10+

£417.61

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 +0.00/-0.25

Angle of Incidence (°):
0

Optical Density OD (Average):
≥4.0

Clear Aperture CA (mm):

45.0

Center Wavelength CWL (nm):

248.00 +3.0/-0.0

Center Wavelength CWL Tolerance (nm):

+3.0/-0.0

Full Width-Half Max FWHM (nm):

10.00 ±2

Full Width-Half Max FWHM Tolerance (nm):

±2

Minimum Transmission (%):

>12

Operating Temperature (°C):

-50 to +50

Coating:

Traditional Coated

Surface Quality:

80-50

Type:

Bandpass Filter

Typical Applications:

KrF Laser Line

Blocking Wavelength Range (nm):

200 - 10000

Construction:

Mounted in Black Anodized Ring

Mount Thickness (mm):

3.5

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

REACH 241:

[Compliant](#)