

[See all 30 Products in Family](#)

## 25.4mm Dia., 400nm, $\lambda/4$ High Energy Waveplate



High Energy Quartz Waveplates

Stock **#39-166** [CONTACT US](#)

⊖ 1 ⊕ £524<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-10	£524.00 each
Qty 11+	£488.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

High Energy Waveplate **Type:**

### Physical & Mechanical Properties

18.0 **Clear Aperture CA (mm):**

25.40 **Diameter (mm):**

**Dimensional Tolerance (mm):**  
+0/-0.2

**Construction:**  
Optically Bonded on UVFS (C7980) Substrate

**Parallelism (arcsec):**  
<3

## Optical Properties

**Coating:**  
 $R_{avg} < 0.25\%$

**Design Wavelength DWL (nm):**  
400

**Substrate:**   
Crystalline Quartz

**Retardance:**  
 $\lambda/4$

**Surface Quality:**  
20-10

**Transmitted Wavefront, P-V:**  
 $< \lambda/10 @ 632.8nm$

**Retardance Tolerance:**  
 $\lambda/200 @ 20^\circ C$

**Damage Threshold, By Design:**   
 $> 20 J/cm^2 @ 1064nm, 10ns, 10Hz$

**Retardance Order:**  
1st

## Threading & Mounting

**Mount Thickness (mm):**  
 $6 \pm 0.2$

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 247:**  
[Compliant](#)

## Product Details

- Damage Threshold up to  $> 20 J/cm^2 @ 1064nm$
- $\lambda/4$  and  $\lambda/2$  Retardance
- Black Anodized Aluminum Mount
- UV to NIR Design Wavelengths Available

High Energy Quartz Waveplates are available in both  $\lambda/4$  and  $\lambda/2$  retardance for discrete laser wavelengths from the UV to NIR and can withstand energy densities up to  $> 20 J/cm^2$  at 1064nm. A large acceptance angle and wide operating temperature range enables these waveplates to be integrated into harsh environments applications. High Energy Quartz Waveplates are mounted in a black anodized aluminum housing for easy identification and system integration.