

TECHSPEC[®] 25.0mm Diameter x 175.0mm FL, 785nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex (PCX) Lenses



Stock **#69-501** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

£45.05

ADD TO CART

Qty 1-9
£45.05
Qty 10+
£40.59
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm): 175.00 @ 587.6nm
Back Focal Length BFL (mm): 172.85
Coating: Laser V-Coat (785nm)
Coating Specification: R _{abs} <0.25% @ 785nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.50 ±0.10
Edge Thickness ET (mm): 2.63
Radius R₁ (mm): 90.47
Clear Aperture CA (mm): 24
f/#: 7.00
Numerical Aperture NA: 0.07
Design Wavelength DWL (nm): 785
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Damage Threshold, By Design: ☐ 5 J/cm ² @ 785nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant