

[See all 3 Products in Family](#)

# 25.4mm Dia. x 12.7mm FL, Uncoated, ISP Optics Silicon (Si) Aspheric Lens | ASPH-SI-25-12

See More by [ISP Optics](#)



Stock #24-881 [CONTACT US](#)

⊖ 1 ⊕ £456.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	£456.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

ASPH-SI-25-12 **Model Number:**

### Physical & Mechanical Properties

25.40 +0.00/-0.13 **Diameter (mm):**

<20 **Centering, ETD (μm):**

22.86	<b>Clear Aperture CA (mm):</b>
0.99	<b>Edge Thickness ET (mm):</b>
4.00 ±0.20	<b>Center Thickness CT (mm):</b>
Protective as needed	<b>Bevel:</b>
Concave	<b>Shape of Back Surface:</b>
<100 Ra	<b>Surface Roughness (□):</b>

## Optical Properties

12.70	<b>Effective Focal Length EFL (mm):</b>
1.00	<b>Numerical Aperture NA:</b>
10.70	<b>Back Focal Length BFL (mm):</b>
<a href="#">Silicon (Si)</a>	<b>Substrate: □</b>
Uncoated	<b>Coating:</b>
60-40	<b>Surface Quality:</b>
0.50	<b>f#:</b>
1200 - 7000	<b>Wavelength Range (nm):</b>
Infinite	<b>Conjugate Distance:</b>
λ/4	<b>Irregularity (P-V) @ 632.8nm:</b>

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
----------------------	------------------------------------

## Product Details

- Transmission from 1.2 - 7µm
- Diffraction-Limited Performance
- Available Uncoated or HDAR Coated for 3 - 5µm

ISP Optics Silicon (Si) Aspheric Lenses provide diffraction-limited performance for weight-sensitive, Mid-Wave Infrared (MMR) applications. Available uncoated for applications in the 1.2 - 7µm range or with a high durability anti-reflection (HDAR) coating in the 3 - 5µm range, these lenses are ideal for harsh environment or black body radiation applications. Silicon features a Knoop Hardness of 1150 making it harder and less brittle than Germanium. ISP Optics Silicon (Si) Aspheric Lenses feature a low density of 2.329g/cm<sup>3</sup>, making them lightweight alternatives to Germanium and Zinc Selenide.