

25.4mm Dia x 150mm FL, Uncoated Meniscus Lens



Stock #72-432 **20+ In Stock**

£22⁴⁰

ADD TO CART

Volume Pricing

Qty 1-9	£22.40 each
Qty 10-24	£20.20 each
Qty 25-49	£18.00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Meniscus Lens **Type:**

Physical & Mechanical Properties

25.40 +0.00/-0.10 **Diameter (mm):**

3.10 ±0.10 **Center Thickness CT (mm):**

<3	Centering (arcmin):
22.86	Clear Aperture CA (mm):
2.00	Edge Thickness ET (mm):

Optical Properties

150.00 @ 587.6nm	Effective Focal Length EFL (mm):
N-BK7	Substrate: <input type="checkbox"/>
5.91	f#:
0.08	Numerical Aperture NA:
Uncoated	Coating:
146.34 @ 587.6nm	Back Focal Length BFL (mm):
587.6	Design Wavelength DWL (nm):
43.36	Radius R ₁ (mm):
95.998	Radius R ₂ (mm):
40-20	Surface Quality:
3 Rings	Power (P-V) @ 632.8nm:
0.5 Rings	Irregularity (P-V) @ 632.8nm:

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Positive Meniscus Lens Designs
- Minimize Spherical Aberration and Reduce Spot Sizes
- 350 – 2,200nm Wavelength Range

Positive Meniscus Lenses are convex-concave lenses manufactured from N-BK7 optical glass and are designed to minimize spherical aberration and reduce spot sizes in focusing applications. When used to focus a collimated beam, the lenses should be oriented with the convex surface towards to light source to minimize spherical aberration. Combining a positive meniscus lens with another lens in a multi-element optical design will allow for a shortening of the focal length and an increase in the numerical aperture (NA) of a system without introducing significant spherical aberrations. Positive Meniscus Lenses are available with focal lengths ranging from 100 to 300mm in 25.4mm diameters sizes, allowing for easy integration into benchtop systems.