

[See all 30 Products in Family](#)

## 25.4mm Dia., 1030nm, $\lambda/4$ High Energy Waveplate



High Energy Quartz Waveplates

Stock #39-176 [CONTACT US](#)

⊖ 1 ⊕ £524.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	£524.00 each
Qty 11+	£488.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

High Energy Waveplate **Type:**

#### Physical & Mechanical Properties

18.0 **Clear Aperture CA (mm):**

25.40 **Diameter (mm):**

**Dimensional Tolerance (mm):**  
+0/-0.2

**Construction:**  
Optically Bonded on UVFS (C7980) Substrate

**Parallelism (arcsec):**  
<3

## Optical Properties

**Coating:**  
 $R_{avg} < 0.2\%$

**Design Wavelength DWL (nm):**  
1030

**Substrate:**   
Crystalline Quartz

**Retardance:**  
 $\lambda/4$

**Surface Quality:**  
20-10

**Transmitted Wavefront, P-V:**  
< $\lambda/10$  @ 632.8nm

**Retardance Tolerance:**  
 $\lambda/300$  @ 20°C

**Damage Threshold, By Design:**   
>20 J/cm<sup>2</sup> @ 1064nm, 10ns, 10Hz

**Retardance Order:**  
0

## Threading & Mounting

**Mount Thickness (mm):**  
6 ±0.2

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 247:**  
[Compliant](#)

## Product Details

- Damage Threshold up to >20 J/cm<sup>2</sup> @ 1064nm
- $\lambda/4$  and  $\lambda/2$  Retardance
- Black Anodized Aluminum Mount
- UV to NIR Design Wavelengths Available

High Energy Quartz Waveplates are available in both  $\lambda/4$  and  $\lambda/2$  retardance for discrete laser wavelengths from the UV to NIR and can withstand energy densities up to >20 J/cm<sup>2</sup> at 1064nm. A large acceptance angle and wide operating temperature range enables these waveplates to be integrated into harsh environments applications. High Energy Quartz Waveplates are mounted in a black anodized aluminum housing for easy identification and system integration.