

TECHSPEC[®] 25.4mm Dia., 1030nm T, 343nm R 0° Yb:doped Ultrafast Harmonic Separator



Ultrafast Harmonic Separators

Stock **#22-677** 20+ In Stock

-

1

+

£244⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£244.00 each
Qty 6-24	£207.20 each
Qty 25-49	£183.20 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Harmonic Beamsplitter

Type:

Physical & Mechanical Properties

>85

Clear Aperture (%):

Construction:

Dichroic	
25.40 +0.00/-0.10	Diameter (mm):
<3	Parallelism (arcmin):
3.00 ±0.10	Thickness (mm):
Optical Properties	
0	Angle of Incidence (°):
Coating Specification: Surface 1: R _{avg} >99% @ 323 - 354nm T _{avg} >98% @ 1000 - 1090nm Surface 2: R _{avg} <0.8% @ 1000 - 1090nm	
343	Reflection Wavelength (nm):
Fused Silica (Corning 7980)	Substrate: ☐
λ/8	Surface Flatness (P-V):
10-5	Surface Quality:
1030	Transmission Wavelength (nm):
GDD Specification: Surface 1: 0±20fs ² @ 323 - 354nm	
Regulatory Compliance	
View	Certificate of Conformance:


Product Details

- Separates Ultrafast Harmonic Wavelengths
- Ultrafast Beamsplitter Coating with Low GDD
- <λ/10 Wavefront Distortion
- Designs for Ti:sapphire and Yb:doped Femtosecond Lasers

TECHSPEC® Ultrafast Harmonic Separators, also known as Ultrafast Harmonic Beamsplitters, are used to reflect the second or third harmonic of femtosecond lasers while transmitting the fundamental pulse. The reflective surface is designed to have high reflectivity and a low Group Delay Dispersion (GDD) of ±20fs² to minimize pulse dispersion. The back surface is coated with an anti-reflection coating to enhance the transmission of the fundamental light. TECHSPEC Ultrafast Harmonic Separators provide low wavefront distortion and feature high quality, thin UV fused silica substrates with 10-5 surface quality. Designs for separating the harmonics of 800nm and 1030nm (Ti:sapphire and Yb:doped fiber) lasers are available.

Please contact us if your application requires an Ultrafast Harmonic Separator designed for custom wavelengths.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts
