

25.4mm Dia. 1064nm  $\lambda$ /4 Quartz Waveplate Multiple Order



Stock **#43-702** 3 In Stock

-

1

+

£283<sup>.20</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | £283.20 each                  |
| Qty 6+         | £228.80 each                  |
| Need More?     | <a href="#">Request Quote</a> |

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Crystalline Waveplate

Type:

Physical & Mechanical Properties

15.00

Clear Aperture CA (mm):

25.40 +0.00/-0.25

Diameter (mm):


|                                                |                                                       |
|------------------------------------------------|-------------------------------------------------------|
| 7.80 +0.00/-0.25                               | Thickness (mm):                                       |
| Crystalline                                    | Construction:                                         |
| <3                                             | Parallelism (arcsec):                                 |
| Optical Properties                             |                                                       |
| Laser V-Coat (1064nm)                          | Coating:                                              |
| 1064                                           | Design Wavelength DWL (nm):                           |
| Crystal Quartz                                 | Substrate: □                                          |
| $\lambda/4$                                    | Retardance:                                           |
| 10-5                                           | Surface Quality:                                      |
| $\lambda/10$ for central 80% of clear aperture | Transmitted Wavefront, P-V:                           |
| $\pm\lambda/200$                               | Retardance Tolerance:                                 |
| 0.0015                                         | Temperature Coefficient ( $\lambda/^\circ\text{C}$ ): |
| 3.5 J/cm <sup>2</sup> @ 1064nm, 10ns           | Damage Threshold, By Design: □                        |
| Multiple Order                                 | Retardance Order:                                     |

|                           |                             |
|---------------------------|-----------------------------|
| Regulatory Compliance     |                             |
| <a href="#">Compliant</a> | RoHS 2015:                  |
| <a href="#">View</a>      | Certificate of Conformance: |
| <a href="#">Compliant</a> | Reach 240:                  |

## Product Details

- Zero Order and Multiple Order Waveplates
- $\lambda/4$  and  $\lambda/2$  Retardance
- Mounted in Black Anodized Aluminum Frame
- [Zero Order Polymer Waveplates](#) Also Available

Quartz Waveplates (Retarders) are available in multiple order and zero order. These waveplates are ideal for a range of applications. Multiple order waveplates are ideal for applications where the wavelength deviates less than  $\pm 1\%$  from the design wavelength of the waveplate. For applications with a greater than  $\pm 1\%$  deviation, zero order waveplates are recommended due to their increased bandwidth and lower sensitivity to temperature change. Quartz Waveplates (Retarders) have the fast axis marked on the edge of the mount to ease system integration.



## Technical Information

