

[See all 4 Products in Family](#)

25.4mm Dia. x 25.4mm FL, Uncoated, ISP Optics Silicon (Si) Aspheric Lens | ASPH-SI-25-25

See More by [ISP Optics](#)



Stock #24-882 CLEARANCE **3 In Stock**

£286⁴⁰

ADD TO CART

Volume Pricing	
Qty 1+	£286.40 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

ASPH-SI-25-25 **Model Number:**

Physical & Mechanical Properties

25.40 +0.00/-0.13 **Diameter (mm):**

<20 **Centering, ETD (µm):**

Clear Aperture CA (mm):

22.86	Edge Thickness ET (mm):
1.73	
<hr/>	
3.00 ±0.20	Center Thickness CT (mm):
Protective as needed	Bevel:
<hr/>	
Concave	Shape of Back Surface:
<100 Ra	Surface Roughness (□):

Optical Properties

25.40	Effective Focal Length EFL (mm):
0.50	Numerical Aperture NA:
<hr/>	
23.15	Back Focal Length BFL (mm):
Silicon (Si)	Substrate: □
<hr/>	
Uncoated	Coating:
60-40	Surface Quality:
<hr/>	
1.00	f#:
1200 - 7000	Wavelength Range (nm):
<hr/>	
Infinite	Conjugate Distance:
λ/4	Irregularity (P-V) @ 632.8nm:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
<hr/>	
Compliant	Reach 240:

Product Details

- Transmission from 1.2 - 7µm
- Diffraction-Limited Performance
- Available Uncoated or HDAR Coated for 3 - 5µm

ISP Optics Silicon (Si) Aspheric Lenses provide diffraction-limited performance for weight-sensitive, Mid-Wave Infrared (MMIR) applications. Available uncoated for applications in the 1.2 - 7µm range or with a high durability anti-reflection (HDAR) coating in the 3 - 5µm range, these lenses are ideal for harsh environment or black body radiation applications. Silicon features a Knoop Hardness of 1150 making it harder and less brittle than Germanium. ISP Optics Silicon (Si) Aspheric Lenses feature a low density of 2.329g/cm³, making them lightweight alternatives to Germanium and Zinc Selenide.