

25.4mm Dia., $\lambda/2$ at 400nm and $\lambda/4$ at 800nm, Dual Wavelength Waveplate



Stock **#23-834** 9 In Stock

-

1

+

£344^{.80}

ADD TO CART

Volume Pricing	
Qty 1-5	£344.80 each
Qty 6+	£313.60 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Dual Wavelength Waveplate

Type:

Physical & Mechanical Properties

18.0

Clear Aperture CA (mm):

25.40 +0/-0.2

Diameter (mm):

+0/-0.2		Dimensional Tolerance (mm):
<30		Parallelism (arcsec):
Optical Properties		
R<0.5% @ 400 & 800nm		Coating:
400, 800		Design Wavelength DWL (nm):
Crystalline Quartz		Substrate: □
λ/2 @ 400, λ/4 @ 800		Retardance:
20-10		Surface Quality:
<λ/10 @ 632.8nm		Transmitted Wavefront, P-V:
λ/100 @ 20 °C		Retardance Tolerance:
>5 J/cm² @ 1064 nm; 10 ns; 10 Hz		Damage Threshold, By Design: □
Multiple order		Retardance Order:
Threading & Mounting		
6 ±0.2		Mount Thickness (mm):
Regulatory Compliance		
Compliant		RoHS 2015:
View		Certificate of Conformance:
Compliant		Reach 247:

Product Details

- λ/4 and λ/2 Retardance for Harmonic Separation
- Designed for Nd:YAG, Yb:YAG, or Ti:Sapphire Lasers
- Multiple Order Designs

Dual-Wavelength Quartz Waveplates are made with high-quality crystalline quartz substrates and offer λ/4 retardance at one wavelength and λ/2 retardance at a second wavelength. Featuring designed wavelengths for Nd:YAG (532 and 1064nm), Yb:YAG (515 and 1030nm), and Ti:Sapphire (400 and 800nm), these waveplates boast high laser damage threshold (LDT) and anti-reflective (AR) coatings for high powered laser applications. Dual-Wavelength Quartz Waveplates are mounted in a 25.4mm black anodized aluminum ring with an 18mm clear aperture. These waveplates are ideal for laser separation applications requiring increased conversion efficiency of dual-wavelength sources or Second-Harmonic Generation (SHG) lasers through management of polarization.