


25.4mm Dia. x 500mm FL, 3-5µm BBAR Coated, ISP Optics Silicon (Si) PCX Lens | HDAR35-SI-PX-25-500

See More by [ISP Optics](#)



Stock **#24-897** CLEARANCE **2 In Stock**

-

1

+

£196⁸⁰

ADD TO CART

Volume Pricing	
Qty 1+	£196.80 each
Need More?	Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Plano-Convex Lens	Type:
HDAR35-SI-PX-25-500	Model Number:
Physical & Mechanical Properties	
	Diameter (mm):

25.40 +0.00/-0.13	
<3	Centering (arcmin):
2.00 ±0.20	Center Thickness CT (mm):
2.00	Edge Thickness ET (mm):
22.86	Clear Aperture CA (mm):
Protective as needed	Bevel:

Optical Properties	
500.00 @4µm	Effective Focal Length EFL (mm):
BBAR (3000-5000nm)	Coating:
R _{avg} <0.5% @ 3 - 5µm R _{abs} <1.5% @ 3 - 5µm	Coating Specification:
Silicon (Si)	Substrate: □
80-50	Surface Quality:
1λ	Irregularity (P-V) @ 632.8nm:
±2	Focal Length Tolerance (%):
1,213.90	Radius R ₁ (mm):
19.69	f/#:
0.03	Numerical Aperture NA:
3000 - 5000	Wavelength Range (nm):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- High-Durability Anti-Reflection (HDAR) Coated for 3 - 5µm
- Ideal for Weight Sensitive Applications
- Available Focal Lengths from 25.4 – 500mm

ISP Optics Silicon (Si) Plano-Convex (PCX) Lenses feature a High Durability Anti-Reflection (HDAR) coating for increased transmission in the 3 - 5µm range. Silicon features a Knoop Hardness of 1150 making it harder and less brittle than Germanium. In addition, the HDAR coating increases the durability of the substrate, enabling use in harsh environments. ISP Optics Silicon (Si) Plano-Convex (PCX) Lenses also feature a low density of 2.329g/cm³, making them ideal for weight-sensitive IR applications such as Near-Infrared (NIR) imaging and infrared spectroscopy.