

TECHSPEC® 25.4mm Dia., 3.18mm Thick, 1064nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors



Stock **#14-340** [CONTACT US](#)

⊖ 1 ⊕ **£141.10**

ADD TO CART

Qty 1-5
£141.10
Qty 6+
£124.95
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mrror

Parallelism (arcmin): <3
Clear Aperture (%): 80
Back Surface: Ground
Reflection at DWL (%): 99.8
Coating Specification: R _{abs} >99.8% @ 1064nm
Wavelength Range (nm): 1046 - 1074
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (1064nm)
Design Wavelength DWL (nm): 1064
Diameter (mm): 25.40 +0.00/-0.10
Thickness (mm): 3.18 ±0.20
Angle of Incidence (°): 0-45
Substrate: ☐ Fused Silica (Corning 7980)
Damage Threshold, Reference: ☐ 15 J/cm² @ 1064nm, 20ns, 20Hz

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View