

TECHSPEC[®]

600-1000nm, 25.4mm Dia. x 50mm EFL, Ultrafast-Enhanced Silver Concave Laser Mirror



TECHSPEC[®] Ultrafast-Enhanced Silver Concave Laser Mirrors

Stock **#13-063** **4 In Stock**

-

1

+

£148⁵⁴

ADD TO CART

Volume Pricing	
Qty 1-5	£148.84 each
Qty 6-9	£131.33 each
Qty 10+	£117.32 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Concave Mirror

Type:

Physical & Mechanical Properties	
25.40 +0.00/-0.20	Diameter (mm):
80	Clear Aperture (%):
6.35 ±0.10	Edge Thickness ET (mm):
Optical Properties	
Fused Silica (Corning 7980)	Substrate: ☐
20-10	Surface Quality:
50.00	Effective Focal Length EFL (mm):
100.00	Radius of Curvature (mm):
Ultrafast-Enhanced Silver (600-1000nm)	Coating:
R _{avg} >99% @ 600 - 1000nm, 0° R _s >99% @ 540 - 1000nm, 45° R _p >98.5% @ 730 - 870nm, 45°	Coating Specification:
0 ±20fs ² @ 600 - 1050nm	GDD Specification:
Ultrafast-Enhanced Silver	Coating Type:
600 - 1000	Wavelength Range (nm):
λ/10	Irregularity (P-V) @ 632.8nm:
0.3 J/cm ² @ 800nm, 48fs, 1 pulse (typical) 0.16 J/cm ² @ 800nm, 48fs, 100Hz, 1000 pulses (typical)	Damage Threshold, Reference: ☐
Regulatory Compliance	
View	Certificate of Conformance:


PRODUCT DETAILS

- Ideal for Focusing Ti:sapphire and Yb:doped Laser Pulses
- Reflectivity >99% at 600 – 1000nm or 800 – 1150nm
- Low Group Delay Dispersion as Low as 0 ±20fs²
- Effective Focal Lengths from 25 to 500mm
- **TECHSPEC® Ultrafast-Enhanced Silver Laser Mirrors** Available

TECHSPEC® Ultrafast-Enhanced Silver Concave Laser Mirrors feature silver coatings that are enhanced with a dielectric coating to provide increased reflectivity at 600 – 1000nm or 800 – 1150nm. These mirrors have an intrinsically low group delay dispersion (GDD) across their wavelength range, making them ideal for focusing or redirecting laser light from femtosecond lasers such as Ti:sapphire and Yb:doped lasers. Their broad wavelength range allows them to be used in applications that require a larger bandwidth than dielectric coated low GDD mirrors can provide. TECHSPEC® Ultrafast-Enhanced Silver Concave Laser Mirrors are available in standard imperial sizes and with effective focal lengths up to 500mm.

Note: TECHSPEC® Ultrafast-Enhanced Silver Concave Laser Mirrors can be designed with different wavelength ranges for other ultrafast laser types.

TECHNICAL INFORMATION



600-1000nm Ultrafast-Enhanced Silver

CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
