

## 25.4mm Dia. 405nm $\lambda/2$ Quartz Waveplate Zero Order



Stock #14-296 **1 In Stock**

⊖ 1 ⊕ £436<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	£436.00 each
Qty 6+	£352.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Crystalline Waveplate

Type:

Air Spaced

Configuration:

### Physical & Mechanical Properties

20.00

Clear Aperture CA (mm):


25.40 +0.00/-0.25	<b>Diameter (mm):</b>
6.00 +0.00/-0.25	<b>Thickness (mm):</b>
Crystalline	<b>Construction:</b>
<3	<b>Parallelism (arcsec):</b>
<b>Optical Properties</b>	
Laser V-Coat (405nm)	<b>Coating:</b>
405	<b>Design Wavelength DWL (nm):</b>
Crystal Quartz	<b>Substrate:</b> <input type="checkbox"/>
$\lambda/2$	<b>Retardance:</b>
10-5	<b>Surface Quality:</b>
$\lambda/10$	<b>Transmitted Wavefront, P-V:</b>
$\pm\lambda/300$	<b>Retardance Tolerance:</b>
0.0001	<b>Temperature Coefficient (<math>\lambda/^\circ\text{C}</math>):</b>
$R_{\text{rms}} < 0.2\% @ 405\text{nm}$	<b>Coating Specification:</b>
0	<b>Retardance Order:</b>

<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>

## Product Details

- Zero Order and Multiple Order Waveplates
- $\lambda/4$  and  $\lambda/2$  Retardance
- Mounted in Black Anodized Aluminum Frame
- [Zero Order Polymer Waveplates](#) Also Available

Quartz Waveplates (Retarders) are available in multiple order and zero order. These waveplates are ideal for a range of applications. Multiple order waveplates are ideal for applications where the wavelength deviates less than  $\pm 1\%$  from the design wavelength of the waveplate. For applications with a greater than  $\pm 1\%$  deviation, zero order waveplates are recommended due to their increased bandwidth and lower sensitivity to temperature change. Quartz Waveplates (Retarders) have the fast axis marked on the edge of the mount to ease system integration.



## Technical Information

