

25.4mm Dia. x 76.2mm FL, Uncoated, ISP Optics Zinc Selenide (ZnSe) Meniscus Lens | ZC-PM-25-76

See More by [ISP Optics](#)



Stock **#24-914** CLEARANCE **4 In Stock**

-

1

+

£373^{.60}

ADD TO CART

Volume Pricing	
Qty 1+	£373.60 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads	
General	
Meniscus Lens	Type:
ZC-PM-25-76	Model Number:

Physical & Mechanical Properties	
25.40 +0.00/-0.13	Diameter (mm):
2.80 ±0.20	Center Thickness CT (mm):
<3	Centering (arcmin):
90	Clear Aperture (%):
22.86	Clear Aperture CA (mm):
2.00	Edge Thickness ET (mm):

Optical Properties	
76.20 @ 10.6µm	Effective Focal Length EFL (mm):
Zinc Selenide (ZnSe), CVD Grade	Substrate: □
3.00	f/#:
0.17	Numerical Aperture NA:
Uncoated	Coating:
600 - 18000	Wavelength Range (nm):
±2	Focal Length Tolerance (%):
179.47	Radius R ₁ (mm):
68.23	Radius R ₂ (mm):
60-40	Surface Quality:
λ/20	Irregularity (P-V) @ 10.6µm:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Positive or Negative Meniscus Lenses
 - CVD Grade Zinc Selenide (ZnSe) Ideal for CO₂ Systems
 - Uncoated or BBAR Coated for 8 – 12µm
- ISP Optics Zinc Selenide (ZnSe) Meniscus Lenses feature positive and negative meniscus designs that minimize spherical aberration. Positive meniscus lenses enable smaller spot sizes than possible with PCXlenses, making them ideal for use in CO₂ laser applications for precise marking or cutting. Negative meniscus lenses are used to increase the focal length when used with additional lenses, decreasing the numerical aperture of an optical system. ISP Optics Zinc Selenide (ZnSe) Meniscus Lenses are available in standard imperial sizes either uncoated or Broadband Anti-Reflection (BBAR) coated for enhanced transmission from 8 – 12µm.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools