

25.4mm Dia. 670nm λ /4 Quartz Waveplate Zero Order



Stock **#46-552**

CLEARANCE

3-4 DAYS

-

1

+

£414.80

ADD TO CART

Qty 1-5
£414.80
Qty 6+
£335.75
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):

15.00

Coating:

Laser V-Coat (670nm)

Design Wavelength DWL (nm):

670

Diameter (mm):

25.40 +0.00/-0.25
Substrate: Crystal Quartz
Retardance: λ/4
Surface Quality: 10-5
Thickness (mm): 7.80 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: λ/10 for central 80% of clear aperture
Parallelism (arcsec): <3
Retardance Tolerance: ±λ/200
Temperature Coefficient (λ/°C): 0.0001
Retardance Order: 0

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View