

**TECHSPEC®**

## 25.4mm H x 25.4mm L x 150mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock #35-026 3-4 DAYS

⊖ 1 ⊕ **£59.50**

**ADD TO CART**

Qty 1-5

£59.50

Qty 6+

£47.60

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):  
150.00

Substrate:   
[N-BK7](#)

**f/#:**  
5.90551181102362

**Numerical Aperture NA:**  
0.08

**Coating:**  
Uncoated

**Type:**  
Cylinder Lens, Plano-Convex

**Wavelength Range (nm):**  
350 - 2200

**Back Focal Length BFL (mm):**  
148.02

**Center Thickness CT (mm):**  
3.00

**Center Thickness Tolerance (mm):**  
±0.1

**Dimensional Tolerance (mm):**  
+0.0/-0.2

**Dimensions (mm):**  
25.4 x 25.4

**Edge Thickness ET (mm):**  
1.95

**Focal Length Tolerance (%):**  
±3

**Radius R<sub>1</sub> (mm):**  
77.52

**Surface Quality:**  
60-40

## Regulatory Compliance

**RoHS:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

---